



# Tobin eye wash systems effective, sterile and safe eyewashes for industrial use

---

DESIGNED FOR FAST APPLICATION WITH  
A LARGE ENOUGH VOLUME FOR MOST EYE  
ACCIDENTS

 **ENWARE**  
installing **confidence**

**Tobin's Eye Wash Systems are proven to be a quick and safe way to flush contaminants from the eyes. This specially designed system gives fast application and a volume large enough for most eye accidents.**

**WITHIN ARMS REACH**

Irrigating the eye within a few seconds of an incident is critical to minimising any damage to the eye. With Tobin, an Eye Wash bottle can be within arms reach.

**CONTROLLED FLOW**

A damaged eye must not be washed with a hard/sharp jet. Tobin's bottles are constructed to empty under natural pressure, giving a soft flow. When the bottom air vent is opened a patient cannot increase the flow by squeezing the bottle.

**VOLUME**

Uninterrupted washing over a long period is particularly important. The specially designed bottles with opened air vent give 3 minutes of continuous flow.

Wall stands for stationary work places or transport stand for mobile units.

1 litre sterile bottles with 3 years shelf life from time of manufacture.



**SIMPLE TO USE**

1. Break Eye Wash outlet
2. Open air vent at the base of the bottle
3. Hold eye lid open
4. 3 minutes of continual flow per bottle (1 Litre)

*In Australia this system is considered supplemental and does not replace the need for a primary Eye Wash station as outlined in AS4775.*



installing**confidence**

**WALL STAND – 5 x 1 LITRE BOTTLE**

- Sterile saline solution
- For stationary work places
- Included 5 Bottles and bracket 39(H) X 45(W) X 10(D)cm
- 5 bottles provides a total 15 minutes of flow

**Order Code: TOB124**



**TRANSPORT STAND**

- Sterile saline solution
- Ideal for vehicles carrying contaminants
- Includes 2 x 1 litre bottles
- 34(H) x 20(W) x 10(D)cm

**Order Code: TOB127**



**WALL STAND – 2 x 1 LITRE BOTTLE**

- Sterile saline solution
- Suitable when space is a problem and/or Eye Washes are required in a number of spots in the same area
- Included 2 Bottles and Stand 39(H) X 20(W) X 10(D)cm

**Order Code: TOB129**



**POCKET EYE WASH BOTTLE**

- Sterile saline solution
- Personally carry in pocket
- Enables washing in seconds
- Contains 200ml sterile saline solution

**Order Code: TOB121**  
**Optional: TOB405 Wire Stand**



**EYE WASH CABINET**

- Sterile saline solution
- A dust protected cabinet suitable for all work places, e.g. industries, building sites, mining, storage facilities etc.
- Includes 2 x 1 litre bottles, cabinet and screws
- 35(H) x 25(W) x 11(D)cm

**Order Code: TOB130**



**REPLACEMENT BOTTLES**

- Sterile saline solution
- Order Code:**  
**TOB128 5 x 1 litre Bottle**  
**TOB126 2 x 1 litre Bottle**

